


# JENSEN MULTISYNC<sup>®</sup>

## Crystal-Controlled Ciblo Motor for Eclair NPR cameras (exchange or conversion)

**MODEL  
508**



### EXCLUSIVE FEATURES:

- Automatic out-of-crystal safety camera stop
- External sync input (slave your Eclair from any pilot source including video tape signals)
- Modification does not change overall camera dimensions in any direction
- Accuracy better than 1/6 frame per 400' ( $\pm 10$  ppm)  $-4^{\circ}\text{F}$  to  $+140^{\circ}\text{F}$
- All controls safety recessed
- Control allows immediate mode change back to camera governor-controlled speed

By this modification, Eclair camera users can now obtain the same advantages in Jensen-engineered crystal frequency control previously available only to Arri-flex operators.

It is, however, necessary that the Ciblo-type Eclair motor be shipped to the Jensen U.S. headquarters, Image Devices Incorporated, Miami, where two options are available: 1) an exchange motor can be shipped promptly from Miami or other Western Hemisphere points with the modifications already installed, or 2) where the user would wish to retain his own motor and

time is not so important, the motor is shipped to the plant where the Multisync elements are added.

Usual turnaround time 30 days.

By and large, the features of the Model 505 Multisync for Arri BL exist in this modification except that the ex-

**MORE**




CONTINUED:

# JENSEN MULTISYNC

MODEL  
508

## Crystal-Controlled Ciblo Motor for Eclair NPR cameras (exchange or conversion)



iciencies of the individual camera design dictate certain variations: e.g., instead of an over-ride button for out-of-crystal-sync recovery, the operator has a control knob to restore pre-modification operation.

Also, framing rate is continuously displayed by LED readout to offset the absence of a tachometer on the Eclair camera.

### SPECIFICATIONS

Operating voltage:	9 to 14 volts from camera battery
Temperature range:	-4°F to +140°F (Minus 20°C to +60°C)
Speed accuracy:	Better than $\pm 10$ ppm ( $\pm 0.001\%$ ) (1/6 frame in 400')
External sync input:	1 volt 50/60 DC
Total added weight	none

SOLE IMPORTER: **Image Devices Incorporated** 811 N.W. 111 Street / Miami, Florida 33168 USA / Cable IMAGEMAMI / Telex 51-9348 / Phone 305/754-4141

YOUR IDI DEALER

